









Quick-Finder – Dynamometer

Readout [d]:	Weighing range	Model	Delivery time (day)								
5 g	5 kg	HDB 5K5N	2		■		■				■
5 g	6 kg	HDB 6K-3XL	2		■		■				
10 g	10 kg	HDB 10K10N	2		■		■				■
10 g	15 kg	HDB 10K-2XL	2		■		■				
10 g	20 kg	HCB 20K10	2		■		■				■
10 g	50 kg	HGA 50K-2S05	2								
20 g	15 kg	CH 15K20	2				■				■
20 g	30 kg	HDB 30K-2XL	2		■		■				
20 g	50 kg	HCB 50K20	2		■		■				■
20 g	60 kg	HCD 60K-2	2		■					■	■
20/50 g	60/150 kg	HCD 100K-2D	2		■					■	■
50 g	50 kg	CH 50K50	2		■		■				■
50 g	99 kg	HCB 99K50	2		■		■				■
50 g	150 kg	HCD 100K-2	2		■					■	■
50 g	150 kg	HFB 150K50	2		■					■	
50/100 g	150/300 kg	HCD 300K-2D	2		■					■	■
100 g	50 kg	CH 50K100	2		■		■				■
100 g	50 kg	HCB 50K100	2		■		■				■
100 g	50 kg	HCN 50K100IP	2		■		■	■	■		■
100 g	200 kg	HCB 200K100	2		■		■				■
100 g	300 kg	HCD 300K-1	2		■					■	■
100 g	300 kg	HFB 300K100	2		■					■	
100/200 g	300/600 kg	HFD 600K-1	2		■			■		■	
0.1/0.2/0.5 kg	300/600/1500 kg	HFD 600K-1	2		■			■		■	
0.2 kg	100 kg	HCB 100K200	2		■		■				■
0.2 kg	100 kg	HCN 100K200IP	2		■		■	■	■		■
0.2 kg	100 kg	HFA 600K-1	2		■					■	■
0.2 kg	100 kg	HFC 600K-1	2		■					■	■
0.2 kg	600 kg	HFB 600K200	2		■					■	
0.2/0.5/1 kg	600/1500/3000 kg	HFD 3T-3	2		■			■		■	
0.5 kg	200 kg	HCB 200K500	2		■		■				■
0.5 kg	200 kg	HCN 200K500IP	2		■		■	■	■		■
0.5 kg	1000 kg	HFA 1T-4	2		■					■	■
0.5 kg	1000 kg	HFC 1T-4	2		■					■	■
0.5 kg	1500 kg	HFO 1.5T0.5M	2	○	■						■
0.5 kg	1500 kg	HTS 1T-4AM	2	○	■						■
0.5 kg	3 t	HFM 3T0.5	2		■					■	
0.5 kg	3 t	HFT 3T0.5	2		■					■	
0.5 kg	5 t	HFM 5T0.5	2		■					■	
0.5/1/2 kg	1500/3000/6000 kg	HFD 6T-3	2		■			■		■	
1 Kg	500 kg	HCB 0.5T-3	2		■						■
1 Kg	3 t	HFA 3T-3	2		■					■	■
1 Kg	3 t	HFC 3T-3	2		■					■	■
1 Kg	3 t	HFO 3T1M	2	○	■						■
1 Kg	3 t	HTS 3T-3AM	2	○	■						■
1 Kg	5 t	HFT 5T1	2		■					■	
1 Kg	10 t	HFM 10T1	2		■					■	
1/2/5 kg	3/6/15 t	HFD 10T-3	2		■			■		■	
2 kg	1 t	HCB 1T-3	2		■						■
2 kg	5 t	HFA 5T-3	2		■					■	■
2 kg	5 t	HFC 5T-3	2		■					■	■
2 kg	6 t	HFO 6T2M	2	○	■						■
2 kg	6 t	HTS 6T-3AM	2	○	■						■
2 kg	10 t	HFT 10T2	2		■					■	
5 kg	10 t	HFA 10T-3	2		■					■	■
5 kg	10 t	HFC 10T-3	2		■					■	■
5 kg	10 t	HTS 10T-3AM	2	○	■					■	■
5 kg	15 t	HFT 15T5	2		■					■	



Package shipment

The time required for internal shipping preparations is shown in days in the pictogram



Verification possible



Adjusting program CAL

For quick setting up of the balance's accuracy. External adjusting weight required



Data interface RS-232

To connect the balance to a printer, PC or network



Hold function:

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



Protection against dust and water splashes IPxx:

The type of protection is specified in the datas.



Stainless steel:

The balance is protected against corrosion



Rechargeable battery pack

Rechargeable set



Battery operation

Ready for battery operation. The battery type is specified for each device